



R-314

Impact gloves with a special grip system for search and rescue operations



Impact

Abrasion Protection



Cut



Light Duty

Durable extrication gloves, featuring a rugged grip system designed for search and rescue

- **Specialized protection:** RINGERS® R314 extrication gloves are developed with a patented TPR (thermoplastic rubber) design and F3 Technology™, ensuring impact protection, comfort and dexterity
- **Enhanced grip:** They feature a special grip system around the palm and fingers, for stronger, longer-lasting grip
- **Added defenses:** Specially designed for search and rescue operations, these RINGERS® gloves also feature Kevlar® stitching around the palm, offering moderate cut resistance
- **Enhanced features:** An extended cuff with gaiter closure helps keep out debris, while their increased visibility material with reflective detailing increases overall hand safety



Industries

- Oil and gas
- Mining
- Emergency Medical Services

Applications

- Rescue extraction from confined spaces
- Operating of heavy machinery
- Crushing and unloading ore
- Shipping and loading of product
- Vehicle Maintenance



R-314

Impact gloves with a special grip system for search and rescue operations

Key Features

- **Patented TPR design:** Knuckles, thumb and finger-length protection
- **Special palm and finger grip system:** For strong, long-lasting grip
- **Increased visibility material:** For impact gloves with added security

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4242BP

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COATING COLOR	PACKAGE
RINGERS® R314	Liner Material: Polyester Cuff Style: Extended cuff with gaiter closure		7, 8, 9, 10, 11, 12, 13	Black	5 pairs/bag, 10 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

