

Datasheet

RS Pro 5.5 kW Manual 3PST DOL Starter, 415 V, 3 Phase, IP55

RS Stock No: **909-4073**



Product Details

RS Pro 5.5 kW manual 3PST DOL starter with steel enclosure, measures 104 x 174 x 134 mm. It has a range of enclosed direct-on-line motor starter which combine high performance and low cost. The range support motors from 0.75 kW to 7.5 kW. It is complete with thermal overload that is fitted for quick easy installing.

Features and Benefits

- Operating temperature range: -5 to +40°C
- Range available as 1-phase or 3-phase model
- Voltage rating of 415 V
- 3-phase 3 PST
- DOL starter
- Compliant with standards BSEN60947-Pt4-Sec 1, BSEN60529-1992 and IEC947-4-1

Specifications:

Additional Features	Colour RAL 7035 Light Grey, Hand Reset Thermal Overloads, Provision for Remote Control
Enclosure	Yes
Motor Starter Functionality	Manual
Motor Starter Type	DOL
Phase	3
Standards Met	BS EN 60947/60529; IEC 947
Overall Depth	134 mm
Overall Length	104 mm
Overall Width	174 mm
IP Rating	IP55
Mounting Type	Surface Mount
Number of Poles	3
Power Rating	5.5 kW
Voltage Rating	415 V ac
Motor Supporting Range	0.75 to 7.5 kW
Operating Temperature	-5 to +40°C