

Features

- Porous Plastic Silencers
- Maximum Input Pressure 6 Bar
- Minimum Operating Temperature -10°C
- Maximum Operating Temperature +50°C

RS PRO Pneumatic Silencers

RS Stock No.: 0631974



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This range of RS PRO Pneumatic Silencers, designed for use with compressed air, pneumatics, and industrial water circuit applications. This high-quality fitting ensures optimum performance for operations that use high pressure and high temperature, without compromising the longevity of the fitting. The pneumatic fitting allows easy connection and installation with other components, saving on valuable time and resource.

General Specifications

Type	Porous Plastic Silencers
Material	POM
Body Material	Polymer
Inlet Connection Type	Threaded
Threaded Inlet Connection Gender	Male
Threaded Inlet Connection	G 1/8 Male
Threaded Inlet Connection Thread Size	1/8 in
Maximum Input Pressure	6 Bar
Minimum Operating Pressure	-10°C
Maximum Operating Pressure	+50°C
Noise Reduction	87 dBa *Noise level in (dB) at 6 bar

Dimensions

F	H	D	L	dB*
1/8	6	15	32.5	87

