



ENGLISH

Datasheet

RS Pro 3 Pair Industrial Cable

RS Stock No: **528-2320**



Product Details

RS Pro 3-pair industrial cable features halogen free polyolefin sheathing, which is flame retardant to BS 4066 and IEC 332 part 3. It gives off low smoke and fume emissions when burnt. This cable is designed to meet the special requirements of high speed data transmission systems associated with data processing or information systems, also for process and control applications.

Features and Benefits

- 3 Pair
- Halogen free polyolefin sheath
- Low smoke and fume emissions when burnt

**Specifications:**

American Wire Gauge	22 AWG
Attenuation	4.1 dB/100 m at 1 MHz
Cable Shape	Twisted Pair
Cable Type	Twisted Pair
Characteristic Impedance	50 Ω
Core Strands	7/0.25 mm
Length	100 m
Number of Pairs	3
Number of Strands	7
Outer Diameter	6.35 mm
Outer Sheath Material	Polyolefin
Reel Length	100 m
Sheath Colour	Grey
Size of Strands	0.25 mm