



Product data sheet

Power tools for trade & industry

Cordless Telescopic Pruner

PRO GKE 18V-25 TP



High-performance cordless chainpole for precision cutting at height

The most important data

Cutter, length	230 mm
Chain speed	7.7 m/s
Chain pitch	.325" (8.25 mm)

Order number 0 600 8D6 000

Technical data

Additional data

Cutter, length	230 mm
Battery recommendation	>=5.5Ah
Chain pitch	.325" (8.25 mm)
Chain speed	7.7 m/s
Chain gauge	1.1 mm



Product data sheet

Power tools for trade & industry

Advantages:

- Cuts tall trees easily thanks to 2.9 m telescopic pole
- Powerful performance with Brushless motor and variable speed control
- Easy maintenance thanks to robust chain tensioning system with magnetic captive nut

