



Product data sheet

Power tools for trade & industry

Orbital Sander

PRO GSS 12V-32



Efficient spot sanding for excellent surface finishings

The most important data

Sanding pad diameter	32 mm
Orbit diameter	3 mm
No-load speed	3000 – 8000 rpm

Part Number 0 601 9L1 000

Technical data

Technical data

Battery voltage	12.0 V
No-load orbital stroke rate	6,000 – 16,000 opm
Orbit diameter	3 mm
Packaging dimensions (width x length x height)	210 x 335 x 98 mm
Weight excl. battery	0.44 kg
No-load speed	3000 – 8000 rpm
BITURBO	No
Sanding pad diameter	32 mm

Noise/vibration information

Sanding panel materials

Vibration emission value ah	2.7 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- High performance with powerful Bosch Professional 12V system and brushless motor
- Excellent ergonomics thanks to small, compact shape and comfortable grip
- Convenient tool operation with HMI for easy speed setting and battery status indication

**HEAVY
DUTY****3000–
8000**
min⁻¹/rpm**L-BOXX
READY****PROFESSIONAL
12V
SYSTEM**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

