

## FEATURES

- Plan Shank
- Various lengths
- HSS for performance and safety
- Perfect for general workshop and maintenance use

## RS PRO HSS Twist Drill Bit, 14mm x 156mm

RS Stock No.: 784-4816



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

Brought to you by RS PRO, a range of jobber drill bits suitable for high-speed metal, wood and plastic drilling. Designed as a twisted drill bit, these attachments guarantee excellent performance and will be an asset to your application. All models are highly reliable and excellent quality.

### General Specifications

<b>Drill Bit Type</b>	Twist Drill Bit
<b>Type</b>	Twist
<b>Material</b>	70% flute length is made of HSS
<b>Surface</b>	Black Finish
<b>Shank Type</b>	Reduced
<b>Drilling Application</b>	Construction, electrical or masonry applications

### Mechanical Specifications

<b>Overall Length</b>	156mm
<b>Point Angle</b>	118°
<b>Diameter</b>	14mm
<b>Flute Length</b>	83mm

RS Art.No.	Dia.(mm)	Overall Length(mm)	Flute Length(mm)
7844816	14.00	156	83
7844810	14.50	156	83
7844829	15.00	156	83
7844822	15.50	156	83
7844826	16.00	156	83
7844835	16.50	156	83
7844838	17.00	156	83
7844832	17.50	156	83
7844841	18.00	156	83
7844844	18.50	156	83
7844848	19.00	156	83
7844857	20.00	156	83

