

# Housing - HC-D 50-TFQ-76/M1PG29G - 1775813

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sleeve housing, for double locking latch, height 76 mm, with screw connection, 1x Pg29, straight cable entry

The illustration shows version HC-D 50-TFQ-76/M 1 PG 21 G



## Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 038366
Weight per Piece (excluding packing)	341.56 g
Custom tariff number	85389099
Country of origin	Germany

## Technical data

### Dimensions

Height	76 mm
Width	56 mm
Length	82 mm
Wrench size, union nut	37 mm
External cable diameter	18 mm ... 27 mm

### Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

### General

Note	For contact inserts HC-D25, A16/A32
Type	D50
Housing type	Sleeve housing
Locking type	For double locking latch
No. of cable outlets	1

# Housing - HC-D 50-TFQ-76/M1PG29G - 1775813

## Technical data

### General

Cable exit	straight
Screw connection	with
Type of the screw connection	1x Pg29
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Cable gland material	Nickel-plated brass
Cable seal material	NBR

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

Approvals

EAC / GL

---

Ex Approvals

## Housing - HC-D 50-TFQ-76/M1PG29G - 1775813

### Approvals

---

Approvals submitted

---

### Approval details

EAC

GL

### Drawings

Dimensional drawing

