



Figure similar

### MLFB-Ordering data

6SL3203-0BE22-0VA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
<b>Input</b>		<b>Line side</b>	
Number of phases	3 AC	Version	screw-type terminal
Line voltage	380 ... 480 V	Conductor cross-section	0,3 ... 10,0 mm <sup>2</sup>
<b>Output</b>		<b>Load side</b>	
Rated current	20.0 A	Version	Screw-type terminals
		Cable length	20.00 m
<b>Mechanical data</b>		<b>PE connection</b>	
<b>Dimensions</b>		Version	On housing with M6 screw studs
Width	60.0 mm		
Height	250.0 mm		
Depth	130.0 mm		
Degree of protection	IP20 / UL open type		
Net weight	2.4 kg		