

PRODUCT DATA SHEET

Philips Coreline LED Spot Fxd Fire Rated WH IP20 6W 4000K

Philips Coreline LED spot kit



Features:-

Brand	Philips Lighting
Order Code	005192
Manufacturer Part No	919913995511
Voltage	240v / Mains Voltage
Dimmable	Yes
Lifetime	40000 Hours
CRI%	>80%
Lumen Output	320
Colour	4000k / 840 / Cool White
Length	145mm
Width	85mm
IP Rating	IP20
Cut Out	64mm
Special Feature	Fixed
Special Feature	Fire Rated
Type	Downlighter
Technology	LED
Wattage	6W
Equiv.Wattage	Halogen 50W
Base	GU10
Beam Angle	40°
Lamp Included	Yes
General Lighting	Yes
Barcode	919913995511



88% Energy Saving

This savings is based purely on a wattage saving. This lamp will last 20 times longer than a traditional lamp.

Product Description

Coreline LED is a range of recessed fixed and fire rated downlights for Philips MASTER LED spot lamps. They come in ready-to-install KIT versions including the MASTER LED spot MV GU10 LED lamp.

These energy saving LED downlights deliver huge energy savings and minimizes maintenance cost without compromising on brightness, enabling owners to achieve a return on their investment within one year.

When you choose the Coreline MASTER LEDspot Kit, you can be sure you're getting a highly energy efficient and cost-effective LED lighting solution. This kit incorporates the Philips MASTER LED lamp which lasts up to 40,000 hours (6W GU10) and allows customers to save up to 85% on their energy bills when compared to halogen. In fact, owners should be able to recoup their investment within just one year.*

There is a range of fittings including fixed LED fire rated downlights and showerproof IP20 and IP65 fire rated LED downlights.

The good news is there is no compromise on light quality when changing to these LED downlights. And the product is great for those hard-to-reach areas where maintenance costs can be high.

* Based upon 6,000 hours burned per year, 10p per unit for electricity and £2 labour cost.



Benefits

- Fire Rated for Installers peace of Mind
- Twist & Lock for easy lamp access
- Loop In Loop out for easier connections
- Improved dimmability compatibility
- Replace your standard fittings with this fixed fire rated version
- Available in simple kit format for easy installation
- Easy to maintain (long lifetime of MASTER LED)
- Available in either matt white or satin nickel finish
- Featuring MASTER LED lamp for improved cost of ownership compared to halogen
- Offers significant energy savings compared to halogen
- Easy to order as lamps are included

Features

- Up to 40K Hours lifetime (6W GU10)
- No driver so less risk of failure
- Philips warranty and best in class after sale service
- Fully tested lamps – Installed in the most demanding environment
- Philips expertise: more than 1 million LED lamps sold to date
- Integrates latest LED technology
- Available in different colour finishes
- Direct lamp access for easy maintenance
- Unique binning technology to make sure all the fittings installed deliver the same quality of light
- Leading lumen output to deliver a true replacement of Halogen Solutions

Applications

- Hospitality
- Retail
- Offices