




---

 PRODUCT-DETAILS

# SPL32/M32/C90

## 90D NPB FITTING M32 32MM-MET




---

**General Information**

Extended Product Type	SPL32/M32/C90
Product ID	7TCA296030R0254
EAN	5020963027260
Catalog Description	90D NPB FITTING M32 32MM-MET
Long Description	90 Degree Conduit Fitting with Fixed External Male Threads, Nomical Conduit Size 32 Millimeters, Thread Size M32, Nickel-Plated Brass

---

**Additional Information**

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

---

**Ordering**

EAN	5020963027260
UPC	786210247113

---

**Technical**


---

Number of Batteries	0
Color	Metallic
Material	Brass
Size	NC 32mm

---



---

**Environmental**


---

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

---



---

**Container Information**


---

Package Level 1 Units	2 piece
Package Level 1 EAN	5020963027260
Package Level 1 Height	7.87 in 200 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	5.9 in 150 mm

---



---

**Certificates and Declarations**


---

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

---



---

**External Classifications and Standards**


---

ETIM 8	EC001180 - Screw connection for protective metallic hose
ETIM 9	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311

---



---

**Categories**


---

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

