

# Product data sheet

Specifications



Earth braids section 10mm<sup>2</sup>,  
length 150mm, eyelet hole 6,4mm.  
Packaging unit: 10.

NSYEB1510D6

## Main

Range	Spacial
Anwendung	Multi-purpose
Product or component type	Earthing braid
Device composition	1 braid
Quantity per set	Set of 10

## Complementary

Material	Tinned copper
Fixing mode	Nut and washer - on earth connection location
Length	150 mm
Width	17 mm
Nominal cross section	10 mm <sup>2</sup>
Diameter	6.5 mm

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	18.0 g
Package 1 Height	1.0 cm
Package 1 width	1.0 cm
Package 1 Length	15.0 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	211.0 g
Package 2 Height	18.0 cm
Package 2 width	6.0 cm
Package 2 Length	1.0 cm
Unit Type of Package 3	PAL
Number of Units in Package 3	400

Package 3 Weight	8.64 kg
Package 3 Height	20.0 cm
Package 3 width	30.0 cm
Package 3 Length	40.0 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------