



Fuse-link, high speed, 225 A, AC 690 V, DC 450 V, 200 kA, BS88, 41 x 113 mm, aR, BS

Part no. **225A 690V AC TYPE T FUSE**  
 Catalog No. **225FM**

### Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	225
Rated voltage			AC 690 V DC 450 V
Construction size			BS88
Size			41 x 113 mm
Utilization category			aR
Breaking Capacity		kA	200
usable for size/applications			protection of DC common bus, DC drives, power converters/rectifiers and reduced voltage starters
Standard/Approval			BS
Shape			offset bolted tags
Standards/Regulations			BS88-4 IEC 60269-4
Optional accessories			fuse-holder BH-1133

### Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	225
Rated voltage		V	690
Voltage type			AC/DC
Rated switching capacity		kA	200
Utilization category			Other
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No