Features

- 3 mm sheet metal frame
- Powder coating application system
- Rubber steering wheels
- Polyurethane rollers
- Galvanised pump body
- Ergonomic tiller
- Sealed bearings 6204 2RS
- 200° rudder rotation

RS PRO Pallet Trucks

RS Stock No.: 0851017



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Hand pallet truck mild steel, capacity 2500 kg forks: mm 685x1000 double rollers

Technical Specifications

Load Capacity (Kg)	2500
Max Lifting Height (mm)	200
Min Lifting Height (mm)	85
Type of Pump	Manual
Forks Length (mm)	1000
Forks Width (mm)	685
Steering Wheels (Ø x mm)	200x50
Type of Rollers	Tandem
Rollers Dimensions (Ø x mm)	82x90
Weight of the Truck (Kg)	69