



Type Number.....	4211	
Designation IEC.....		
System.....	Manganese Dioxide/ Zinc/KOH-Electrolyte	
Nominal Voltage.....	6 V	
Typical Capacity C [mAh].....	55 (discharge with high-resistance)	
Weight (approx.).....	4.30 g	
Volume.....	---	
<b>Temperature Ranges</b>	min	max.
Storage.....	-10°C	60°C
Discharge.....	-10°C	60°C
<b>Dimensions</b>	min	max.
Diameter.....	9.62	10.22
Height (B).....	15.50	16.50
Shoulder Diameter [F]	5.20	5.80
Shoulder Height [G]		0.50



**Typical Capacities (at 20°C)**

Discharge Type	Load	End Voltage:	3.6 V
Continuous 24h/d, 7d/w	20000 Ω	Time:	210 h

**No publication or circulation of data to third parties without consent of VARTA Consumer Batteries**