

ZCKE656

limit switch head ZCKE - side steel roller
plunger vertical - -40 °C



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJ9H29 ZCKJ11H29 ZCKJ8H7 ZCKJ2H7 ZCKJ2H29 ZCKJ8 ZCKJ5H7 ZCKJ21 ZCKJD31 ZCKJ6H29 ZCKJD37H29 ZCKJ11H7 ZCKJ6 ZCKJ7H29 ZCKJ6H7 ZCKJD35H29 ZCKJD39 ZCKJ21H7 ZCKJ1H7 ZCKJD31H7 ZCKJD37H7 ZCKJ9 ZCKJ9H7 ZCKJ7H7 ZCKJD39H29 ZCKJ2 ZCKJ5 ZCKJ11 ZCKJD31H29 ZCKJ1 ZCKJD39H7 ZCKJD35H7 ZCKJD37 ZCKJ5H29 ZCKJD35 ZCKJ8H29 ZCKJ7 ZCKJ21H29 ZCKJ1H29
Movement of operating head	Linear
Type of operator	Side roller plunger spring return metal (with vertical roller)
Type of approach	Vertical approach, 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With
Net weight	0.205 kg
Head material	Metal

Environment

Ambient air temperature for operation	-40...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Low temperature

Packing Units

Package 1 Weight	186 g
Package 2 Weight	9.644 kg

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------