



Product number 1171250341
EAN 4007123684878

DESCRIPTION

- LED spotlight with super-bright Everlight SMD LEDs and flat design.
- User-friendly mounting due to external, waterproof spring-loaded clamp.
- Front cover made of safety glass.
- Solid, modern aluminium housing.
- Adjustable mounting bracket.

TECHNICAL DATA

Luminous flux	3450 lm	With motion detector	No
Power consumption	30 W	With socket outlet	No
Luminous efficacy	136 lm/W	Impact strength	IK08
Energy efficiency class		Protection class	I
Colour rendering index	80-89 (class 1B)	Degree of protection (IP)	IP65
Min.-Max. Nominal input voltage	220 V - 240 V	Basic colour	black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.76 kg
Weight of product (without packaging)	0.67 kg	Dimension LxWxH (incl. packing)	6 cm x 19.5 cm x 15 cm
Dimension LxWxH (without packing)	4 cm x 18.5 cm x 14.5 cm		

SCOPE OF DELIVERY

LED Light JARO 4060