

## M18 ONEPD2-502X | M18 FUEL™ ONE-KEY™ percussion drill



- Higher power efficiency under load - outstanding torque of 135 Nm
- Extremely compact design of 175 mm length for access into tight spaces
- Advanced heavy duty chuck providing increased bit grip
- Connect via Bluetooth® with the ONE-KEY™ app
- Customise anti-kickback control via ONE-KEY™ app
- ONE-KEY™ tool tracking & security offers a cloud-based inventory management platform that supports both location tracking and theft prevention
- Save up to 4 custom settings to the tools memory for fast selection on the jobsite

No load speed (rpm)	0 - 550/ 0 - 2000
Chuck capacity (mm)	13
Max. drilling wood/ steel/ masonry (mm)	89/ 16/ 16
Max. percussion rate (bpm)	0 - 32,000
Max. torque (Nm)	135
Kit included	2 x 5.0 Ah Battery packs, M12-18 FC Charger, HD Box
Article Number	4933464527