

Drive shaft adapter
EAMB-24-9-15X21-16X20
Part number: 1344642



 [General operating condition](#)

Data sheet

Feature	Value
Mounting diameter 1	15 mm
Mounting diameter 2	16 mm
Size	80
Nominal length	21 mm
Mounting position	optional
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	3.1 kgmm ²
Transmittable torque	29 Nm
Product weight	72 g
Note on materials	RoHS-compliant