

VS-PPC-F2-MSTB-MNNA-1R-SPSA5 - Panel-mount frame



1608249

<https://www.phoenixcontact.com/pc/products/1608249>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Push/pull panel mounting frame, metal, version 14, including contact insert with spring-cage connection, fixed 24 V coding according to Guideline for PROFINET, for rectangular mounting cutout, with seal, without fixing screws

Commercial data

Item number	1608249
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABNOJA
Catalog page	Page 364 (C-2-2019)
GTIN	4046356160049
Weight per piece (including packing)	63.4 g
Weight per piece (excluding packing)	60 g
Customs tariff number	85366990
Country of origin	DE

VS-PPC-F2-MSTB-MNNA-1R-SPSA5 - Panel-mount frame



1608249

<https://www.phoenixcontact.com/pc/products/1608249>

Technical data

Product properties

Product type	Panel-mount frame
Type	MSTB
Number of positions	5
Type	Male

Insulation characteristics

Degree of pollution	2
---------------------	---

Electrical properties


Rated voltage (III/3)	24 V
Rated current	16 A (at 20 °C)
Transmission medium	Copper

Connection data

Connection technology

Connection method	Spring-cage connection
-------------------	------------------------

Dimensions

Dimensional drawing	
Width	36.2 mm
Height	42 mm
Length	41.9 mm

Material specifications

Color	silver
Material	Metal
Flammability rating according to UL 94	V0
Seal material	NBR
Seal material	NBR
Housing material	Metal
Housing surface material	nickel-plated
Contact surface material	Au/Ni

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

1608249
<https://www.phoenixcontact.com/pc/products/1608249>

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 70 °C

Mounting

Mounting type	Front mounting
---------------	----------------

VS-PPC-F2-MSTB-MNNA-1R-SPSA5 - Panel-mount frame




1608249

<https://www.phoenixcontact.com/pc/products/1608249>

Drawings

Dimensional drawing



Mounting cutout

1608249
<https://www.phoenixcontact.com/pc/products/1608249>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/pc/products/1608249>

 UL Recognized Approval ID: E118976				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	24 V	16 A	- 14	-

1608249
<https://www.phoenixcontact.com/pc/products/1608249>

Classifications

ECLASS

ECLASS-12.0	27440210
ECLASS-13.0	27440210

ETIM

ETIM 9.0	EC002310
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-PPC-F2-MSTB-MNNA-1R-SPSA5 - Panel-mount frame



1608249

<https://www.phoenixcontact.com/pc/products/1608249>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	4c4a0bf8-ed6d-40ed-af0a-97af66398454

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com