

# PRASD3-16F-BB0GW ✓ ACTIVE

Alcoswitch

TE Internal #: 1571079-9

High Power Rocker Switch, Panel Mount, 13 x 19.2 mm [.514 x .754 in] Panel Cutout, Silver Contact Plating

[View on TE.com >](#)



Switches > Rocker Switches



Switch Type: **High Power Rocker Switch**

Product Mount Type: **Panel Mount**

Indicator/Imprint Legend: **I O II**

Panel Cutout Size: **13 x 19.2 mm [.514 x .754 in]**

Switch Contact Plating Material: **Silver**

## Features

### Product Type Features

Switch Type	High Power Rocker Switch
Actuator Type	Top
Actuator Style	Rocker
Switch Connection Type	Quick Connect Terminal

### Configuration Features

Indicator/Imprint Legend	I O II
Panel Cutout Size	13 x 19.2 mm [.514 x .754 in]
Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On Off On

### Electrical Characteristics

Contact Current Rating	16 A
Operating Voltage Range	125 VAC

### Body Features

Product Orientation	Vertical
---------------------	----------



Actuator Color	Black
----------------	-------

### Contact Features

Terminal Tab Width	4.75 mm[.187 in]
--------------------	------------------

Switch Contact Plating Material	Silver
---------------------------------	--------

### Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

### Housing Features

Process Sealed	No
----------------	----

### Industry Standards

Compatible With Agency/Standards Products	VDE
-------------------------------------------	-----

Compatible With Approved Standards Products	UL E46765
---------------------------------------------	-----------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
-----------------------------------------------	-----------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
----------------------------------------	-------------------------------------------------------------------------------------------------------------------------------

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	-------------------------------------------------------------------------------------

Solder Process Capability	Not applicable for solder process capability
---------------------------	----------------------------------------------

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Customers Also Bought



## Documents

### Product Drawings

[PRASD3-16F-BB0GW=POWER ROCKER](#)

English

### CAD Files

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_1571079-9\\_N.3d\\_igs.zip](#)

English



**Customer View Model**

[ENG\\_CVM\\_CVM\\_1571079-9\\_N.3d\\_stp.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1571079-9\\_N.2d\\_dxf.zip](#)

English

**3D PDF**

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Datasheets & Catalog Pages**

[SWITCHES\\_CORE\\_PROGRAM\\_CATALOG](#)

English

[1654742\\_HOUSEHOLD\\_APPLIANCES\\_RAST5](#)

English