

Datasheet

RS Pro 6 Digit, Digital, Counter, 10Hz, 24 V dc

RS Stock No: **896-7015**



Product Details

RS Pro counter with 6 digit display, has frequency of 10 Hz and supply voltage of 24 V dc. This electronic impulse counter is compact in size, making them ideal where space is limited and is suitable for panel mounting.

Features and Benefits

- 6-digit (4 mm)
- Compact size and robust design
- Resettable and non-resettable models available
- 3 mounting options - Panel, bail and base
- Push button quick reset
- High accuracy and reliability
- Requires no lubrication or maintenance
- Optional locking for reset button
- Wide supply voltage range
- IP30 protection

Specifications:

Approvals	CE; RoHS Compliant
Count Mode	Pulse
Function	Impulse Counter
Meter Type	Electronic
Cutout Height	25.7 mm
Cutout Width	50.8 mm
Depth	63.2 mm
Maximum Count Frequency	10 Hz
Measurement Range	0 to 999999
Minimum Measurement	0
Minimum Operating Temperature	-5°C
Number of Digits	6
Connection Type	Terminal Strip
Cutout Size	50.8 x 25.7 mm
Digit Height	4 mm
Display Type	Digital
Input Type	Voltage
Mounting Type	Panel Mount
Reset Method	Manual
Supply Voltage	24 V dc