

Features

- Mounting Block with Pressure Gauge
- Excellent readability (63mm dial)
- Fast and easy installation
- Stainless steel case, providing good corrosion resistance.
- Accuracy: $\pm 2.5\%$ of full scale

RS PRO Pressure Gauge & Mounting block

RS Stock No.: 0291728



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Pressure Gauges are calibrated with a dual scale for reading MPA or PSI.

- Excellent readability (63mm dial)
- Fast and easy installation
- Stainless steel case, providing good corrosion resistance.
- Accuracy: $\pm 2.5\%$ of full scale

Note

Working pressure quoted is the maximum acceptable system pressure.

General Specifications

Accessory Type	Mounting Block with Pressure Gauge
Connector A	NPT1/4 Male
Connector A - Gender	Male
Connector A - Thread Size	1/4in
Connector A - Thread Standard	NPT
Connector B	NPT3/8 Female
Connector B - Gender	Female
Gauge Port	NPT1/4 Female
Mounting Block Material	40#Cr
Pressure Gauge Material	Stainless Steel
Working Pressure	0-70MPA(0-700BAR)
Measuring Range	0-100MPA(0-1000BAR)
Display Type	Analogue
Best Accuracy	$\pm 2.5\%$
Dial Diameter	63MM
Case Material	Stainless Steel
Mounting Block Connector	NPT1/4 Male and NPT3/8 Female

Approvals

Compliance/Certifications	CE, EN ISO 12100:2010, EN 809:1998+A1:2009
Declarations	UKCA
Production Standard	GB1226-1227

Unit: mm

Tolerance: +/-2%

