

Datasheet

**RS Pro Stainless Steel Adjustable Height Mount 46mm
Vulcanised Rubber 35mm 15mm 53mm 75kg 38mm M10 0°
RS Stock No: 442-678**



Product Details

RS Pro stainless steel adjustable height mount is specially developed for lighter equipment such as wood processing machines, compactors, light industrial machinery, office equipment and domestic appliances. This light duty mount consists of levelling bolts with vulcanized rubber feet which guarantees safe and reliable installation on most surfaces. This mount can be fitted both in internal and external holes in the machine frame and chassis.

Features and Benefits

- Withstands lighter loads
- Wide range suitable for most applications
- 75 kg static load capacity
- Vulcanised rubber foot



ENGLISH

Specifications:

Base Material	Stainless Steel
Diameter	46 mm
Foot Material	Vulcanised Rubber
Maximum Adjustment Height	35 mm
Minimum Adjustment Height	15 mm
Overall Height	53 mm
Static Load Capacity	75 kg
Thread Length	38 mm
Thread Size	M10
Tilt Angle	0°