

Technical Data Sheet

FrogTape® Delicate Surface Masking Tape

A low tack masking tape for use on freshly painted surfaces, most wallpapers, and newly plastered walls



Properties

- Leaves only the sharpest, cleanest lines
- Can be applied for up to 60 days in direct sunlight (UV resistant)
- Low tack for delicate surfaces
- With PaintBlock® Technology - Reduces paint bleed
- Remove immediately after painting

Area of Use

- Designed for use when painting with emulsion paint
- Available in 24mm, 36mm and 48m widths
- Available in 55m lengths, single packs and multi-pack

Technical Data

Thickness mm	: 0,08
Adhesive	: Synthetic Rubber
Adhesion to Stainless Steel N/10mm	: 2,74
Elongation	: 5.0%
Tensile Strength N/10mm	: 33,3
Service Temperature Min	: 10°C

Application Overview

Application	Suitability
Inside	☐
Outside	☐
Fresh Paint (dried 24 hours min.)	☐
Wallpaper (coated)	☐
Treated Wood	☐
Newly Plastered Walls	☐
Veneer, Laminate, Vinyl	☐

☐ suitable

Storage and Usage Conditions

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

Physical and performance characteristics shown above are obtained by tests recommended by PTSC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Services Department and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages.

The user should determine whether a product is fit for a particular purpose and is suitable for the user’s method of application before use.