

FEATURES

- Glass clear transparency
- Excellent abrasion and corrosion properties
- Good flexibility
- EC compliant for food applications
- Suitable for use with alcohol, petrol, oils, greases and solvents
- Highly resistant to a wide range of acids and alkalis
- Manufactured from cadmium and silicone-free materials using a special low toxic

RS PRO PVC Flexible Tubing, Transparent, 14mm External Diameter, 25m Long, 126mm Bend Radius, Alcohol, Grease, Oil,

RS Stock No.: 797-350



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

This RS Pro clear PVC hose is suitable for a wide range of applications such as for low-pressure food and general industrial based environments. The hose is manufactured from the highest quality, low-toxic materials to give excellent clarity, flexibility and durability over a wide temperature range. The highly flexible hose supports use in both open and tight spaces and with excellent corrosion and abrasion properties, this PVC hose is a durable and reliable tool in any application.

General Specifications

| Material | PVC |
|-------------|---|
| Colour | Transparent |
| Reinforced | No |
| Application | Alcohol, Grease, Oil, Petrol, Solvent, General industrial applications; Scientific; Pharmaceutical; Medical |

Mechanical Specifications

| Inner Diameter | 8mm |
|----------------|-------|
| Outer Diameter | 14mm |
| Length | 25m |
| Bend Radius | 126mm |
| Safety Factor | 3:1 |

Operation Environment Specifications

| Minimum Operating Temperature | -15°C |
|-------------------------------|-------|
| Maximum Operating Temperature | +60°C |
| Maximum Working Pressure | 4 bar |



Approvals

Compliance/Certifications

RoHS compliant

