

Lawn Mower XGT®

LM002G

Model LM002G is a 530mm (21") cordless lawn mower powered by 40Vmax XGT® Li-Ion battery (two in parallel).

This model features increased convenience, such as automatic switching from one battery to the other battery connected in parallel. Other features and benefits are: Steel cutting deck, Three cutting modes: Normal, Soft no-load, Noise reduction, Rigid handle foldable without tool, Equipped with self-propelled function.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	2300 - 2800 min ⁻¹
Cutting height positions	10
Width of Mowing Deck	53,4 cm
Mowing Height	20 - 100 mm
Steel Mowing Deck	✓
Rear Wheel Diameter	23 cm
Front Wheel Diameter	23 cm
RPM (Normal mode)	2800 min ⁻¹
RPM (Soft no load mode)	2300 / 2800 min ⁻¹
RPM (noise reduction mode)	2300 min ⁻¹
Actual mowing area 8.0 Ah x 2	2500 - 3400 m ²

User benefits

- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Self-propelled for reduce operator fatigue

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing