



SC-5 0240

E1441279

SPLICING CONNECTOR, 5-CONDUCTOR 0.2-4.0mm2, AWG 28-12, WITH LEVER



Product Properties:

Nominal voltage	450 V
Nominal current	32 A
Transparent	Yes
Number of clamp positions	5 .
With operation lever	Yes
Suitable for solid core	Yes
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Colour	Green
Operating temperature	-40-105 °C
Connector type	Toppklämma, öppningsbar
Inflammability class of insulation material according to with UL94	V2

Dimensions:

Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.2-4 mm²
Conductor cross section solid (solid, stranded)	0.2-4 mm²
MOQ	25 .
Unit	pcs
Nominal cross section	0.2-4 mm²
AWG-range	28-12 .

Nominal voltage	450 V
-----------------	-------

Approvals:

Approved according to CE	Yes
Approved according to UKCA	Ja
Inflammability class of insulation material according to with UL94	V2

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	Compliance
REACH	No SVHC (Latest. 21 Jan 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Skarv & Toppklämmor - Standard Pack
Search Description	SKH2023ERIK1 ENR2023V ANSLUTNINGSKLÄMMA
Alternative SKU	SC-50240
E-no	E1441279

Logistic information:

Barcode	733117641159
Country of origin	CN
E-no	E1441279
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	25 .
Stock code	SC-5 0240
Taric code	85369010
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.