



Smoke detector with sealed , Lithium battery, battery lifetime 10 year

Model		
type of certification NCP	No	
cable entry type	Not applicable	
design of the power supply	Battery/rechargeable battery	
design of fire alarm smoke detector	Yes	
design of the product explosion-proof design	No	
design of the sensor	Other	
design of transmission medium wireless transmission	No	
General technical data		
response value temperature	40 °C	
outer diameter of the enclosure	105 mm	
loudness level	85 dB	
Supply voltage		
type of voltage of the supply voltage	DC	
Appearance		
RAL color number	9010	
color	white	
Product details		
product component integrated orientation lighting	No	
product extension optional can be networked with radio connection	No	
Product function		
product function		
• of backup battery rechargeable	No	
• of the button	Test button	
Number		
number of fire alarms networkable	1	
Mechanical Design		
height	35 mm	
length	105 mm	
fastening method	mounting plate	
fastening method mounting in special cable duct	No	
Approvals Certificates		
General Product Approval	other	Dangerous goods

[Miscellaneous](#)



[Miscellaneous](#)



[Confirmation](#)

[Dangerous goods in-formation](#)

Environment

[Environmental Conformations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TC1292-8>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TC1292-8>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TC1292-8

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

3/12/2024 

