Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



WHITE LED PILOT LIGHT 120V 30MM T-SKP

Local distributor code: 387212809

9001SKP38LWW9

EAN Code: 3389118037274

Main

| Range of product | Harmony 9001SK |
|---------------------------|--------------------|
| Product or component type | Pilot light |
| Device short name | 9001SK |
| Lens type | Domed plastic |
| Light block supply | Direct 120 V AC/DC |

Complementary

| Plastic |
|--|
| 30 mm |
| Round |
| White |
| LED |
| BA 9s |
| 120 V AC/DC |
| 0.8 N.m conforming to IEC 60947-1 |
| Cross slotted |
| Screw clamp terminals, 1 x 0.222 x 1.5 mm² conforming to IEC 60947-1 |
| 10 A |
| 10 A cartridge fuse conforming to IEC 60947-5-1 |
| 250 V (pollution degree 2) conforming to IEC 60947-1 |
| 2.5 kV conforming to IEC 60947-1 |
| Any position |
| 54 mm |
| 70 mm |
| 42 mm |
| 0.082 kg |
| Complete product |
| Domed |
| 120 V |
| White |
| Polycarbonate |
| |

| Size | 30 mm |
|--------------|-------|
| Light source | LED |

Environment

| Electrical shock protection class | Class II conforming to IEC 61140 | |
|---------------------------------------|---|--|
| Protective treatment | TC | |
| IP degree of protection | IP66 conforming to IEC 60529 | |
| NEMA degree of protection | NEMA 1 | |
| | NEMA 12 | |
| | NEMA 13 | |
| | NEMA 2 | |
| | NEMA 3 | |
| | NEMA 3R | |
| | NEMA 4 | |
| | NEMA 4X | |
| Vibration resistance | 7 gn (f= 2500 Hz) conforming to IEC 60068-2-6 | |
| Shock resistance | 50 gn conforming to IEC 60068-2-27 | |
| Ambient air temperature for operation | -2570 °C | |
| Ambient air temperature for storage | -4070 °C | |
| Standards | UL 508 | |
| | JIS C 852 | |
| | IEC 60947-5-4 | |
| | JIS C8201-5-1 | |
| | IEC 60947-1 | |
| | CSA C22.2 No 14 | |
| | IEC 60947-5-1 | |
| | JIS C8201-1 | |
| Product certifications | UL 508 | |
| | NEMA | |

Packing Units

| Unit Type of Package 1 | PCE |
|------------------------------|----------|
| Number of Units in Package 1 | 1 |
| Package 1 Height | 5.588 cm |
| Package 1 Width | 4.572 cm |
| Package 1 Length | 9.398 cm |
| Package 1 Weight | 81.647 g |

Logistical informations

Country of origin

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability

| Environmental footprint |
|-------------------------|
|-------------------------|

Environmental Disclosure

Product Environmental Profile

Use Better

| Packaging made with recycled cardboard | Yes |
|--|--|
| Packaging without single use plastic | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| REACh Regulation | REACh Declaration |

Use Again


| ○ Repack and remanufacture | |
|----------------------------|---|
| Circularity Profile | End of Life Information |
| Take-back | No |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Product datasheet

9001SKP38LWW9

Dimensions Drawings

Dimensions



e panel thickness: 1 to 6 mm / 0.04 to 0.24 in.

9001SKP38LWW9

Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony 9001SK



Offer Marketing Illustration

Product benefits / Features

