

PVC Cable	No. of Cond.	AWG	Jacket Characteristics	ID Number	Ship Wt. (lbs)	Cond. Colors	Shield	UL	CSA	Type	MSHA	Temp. (°C)
	10	18	10 mm OD, PVC, YE, 300 V	RF50607-30M RF50607-100M RF50607-200M	11 35 70	GN/YE, BN, BU, WH, YE, GN/WH, BN/WH, BU/WH, OG, GY, Drain (20)	Foil/Drain	•	•	AWM 2517	•	105° -40°
	10	24	7.0 mm OD, PVC, BK, 300 V	RF50836-30M RF50836-100M RF50836-200M	5 16 31	GN, GY, VT, BU, YE, BK, WH, RD, PK, BN, Drain (26)	Foil Drain	•	•	AWM 2517	•	105° -40°
	10	24	6.6 mm OD, PVC, BK, 300 V	RF51076-30M RF51076-100M RF51076-200M	5 16 31	GN, GY, OG, BU, YE, TN, WH, RD, PK, BN, Drain (26)	Foil/Drain	•	•	AWM 2517	•	105° -40°
	10	24	7.2 mm OD, PVC, GY, 300 V	RF51006-30M RF51006-100M RF51006-200M	6 18 35	OG, RD, BU, PK, GY, YE, GN, BN, WH, TN, Drain (26)	Foil/Drain Braid	•	•	AWM 2517	•	105° -40°
	10	24	6.2 mm OD, PVC, GY, 300 V	RF51004-30M RF51004-100M RF51004-200M	4 13 26	OG, RD, BU, PK, GY, YE, GN, BN, WH, TN		•	•	AWM 2517	•	105° -40°
	11	18 22	8.5 mm OD, PVC, YE, 300 V	RF50624-30M RF50624-100M RF50624-200M	9 30 60	(18 = BN, BU, GN/YE), (22 = WH/GN, GN, GY, WH, RD/BU, YE, GY/PK, BN/GN, Drain (22)	Foil/Drain	•	•	PLTC AWM 2517	•	105° -30°
	11	18	10 mm OD, PVC, BK, 300 V	RF50716-30M RF50716-100M RF50716-200M	12 38 75	BK, GN, OG, BU, RD, WH, WH/BK, RD/BK, GN/BK, OG/BK, BU/BK, Drain (20)	Foil/Drain	•	•	AWM 2517	•	105° -40°
	11	18	10 mm OD, PVC, YE, 600 V	RF50913-30M RF50913-100M RF50913-200M	12 38 75	WH, GN, YE, GY, PK, RD, BK, VT, BU, BN, GN/YE, Drain (20)	Foil/Drain	•	•	AWM 2586	•	105° -40°
	11	18	10.5 mm OD, PVC, YE, 300 V	RF51088-30M RF51088-100M RF51088-200M	13 42 83	WH, GN, YE, GY, PK, RD, BK, VT, BU, BN, GN/YE, Drain (20)	Foil/Drain	•	•	ITC/PLTC AWM 2517	•	105° -30°
	11	18	11.2 mm OD, PVC, YE, 300 V	RF51190-30M RF51190-100M RF51190-200M	13 44 87	BN, BU, WH, GN, YE, GY, PK, RD, BK, VT, GN/YE, Drain (20)	Foil/Drain Braid	•	•	ITC/PLTC AWM 2517	•	105° -30°
	12	16	13.2 mm OD, PVC, YE, 600 V	RF51035-30M RF51035-100M RF51035-200M	20 65 130	GN, OG, BU, WH/BK, RD/BK, GN/BK, OG/BK, BU/BK, BK/WH, WH, RD, BK		•	•	ITC/PLTC AWM 2586	•	105° -30°
	12	18	10 mm OD, PVC, YE, 300 V	RF50606-30M RF50606-100M RF50606-200M	12 38 75	BU/WH, GN/YE, BN, BU, WH, OG, YE, GN/WH, BN/WH, GY, PK, RD, Drain (20)	Foil/Drain	•	•	AWM 2517	•	105° -40°
	12	22	7.6 mm OD, PVC, BK, 300 V	RF50967-30M RF50967-100M RF50967-200M	6 20 40	RD, PK, YE, GN, WH, BU, BN, OG, BK, GY, TN, VT, Drain (24)	Foil/Drain	•	•	AWM 2517	•	105° -40°
	12	24	7 mm OD, PVC, BK, 300 V	RF50755-30M RF50755-100M RF50755-200M	5 16 32	RD, GN, OG, TN, GY, VT, YE, BK, WH, BN, BU, PK, Drain (26)	Foil/Drain	•	•	AWM 2517	•	105° -40°
	12	24	7.0 mm OD, PVC, YE, 300 V	RF50917-30M RF50917-100M RF50917-200M	5 16 32	BK, RD, GN, GY, PK, RD/BU, GY/PK, BU, VT, WH, YE, BN, Drain (26)	Foil/Drain	•	•	AWM 2517	•	105° -40°
	12	24	7.2 mm OD, PVC, GY, 300 V	RF50988-30M RF50988-100M RF50988-200M	6 19 38	BN, WH, OG, RD, BU, PK, GY, YE, GN, BK, TN, VT, Drain (26)	Foil/Drain Braid	•	•	AWM 2517	•	105° -40°
	12	24	6.3 mm OD, PVC, GY, 300 V	RF50991-30M RF50991-100M RF50991-200M	5 15 29	BN, WH, OG, RD, BU, PK, GY, YE, GN, BK, TN, VT		•	•	AWM 2517	•	105° -40°
	14	18	10.6 mm OD, PVC, YE, 300 V	RF50576-30M RF50576-100M RF50576-200M	14 45 90	GN/YE, GN/WH, BN, BN/WH, BU, BU/WH, WH, YE, PK, BK, OG, GY, RD, VT, Drain (20)	Foil/Drain	•	•	AWM 2517	•	105° -40°
	14	18	11.2 mm OD, PVC, YE, 600 V	RF51097-30M RF51097-100M RF51097-200M	14 47 93	PK, YE, WH, GY/PK, BU, GN, RD/BU, GY, RD, VT, GN/YE, BK, BN/GN, BN		•	•	AWM 2586	•	105° -40°