



ENGLISH

Datasheet

RS Pro 1500mm x 12mm 304S15 Stainless Steel Square Bar

RS Stock No: **661-4816**



Product Details

RS Pro stainless steel square bar measures 1500 mm x 12 mm. It is a general purpose non-magnetic stainless steel bar possessing good weldability, formability and general corrosion resistance. It is perfect for food and dairy processing equipment, laundry and chemical industry, process plant and tanks.

Features and Benefits

- Bar-rolled edge
- Rod - BS970 pt 3 BSEN 10088-3
- Angle - BS970 pt 1 BSEN10051
- Square - BS970 pt 3 BSEN 10088-3
- Sheet - BS1449 pt 2 BSEN 10088-2 (2B surface finish)
- Excellent material for polishing

**Specifications:**

Form	Square Bar
Hardness	92 HB
Material	304S15 Stainless Steel
Suitability	Food & Dairy Processing Equipment, Laundry & Chemical Industry, Process Plant & Tanks
Density	8 g/cm ³
Height	12 mm
Length	1.5 m
Thermal Conductivity	16.2 W/mK at 100°C
Width	12 mm
Tensile Strength	520
Stainless Steel	304 (A2)