

MC512PA Terminal Block Markers

Pre-printed marker card for horizontal terminal block assembly



5.2 mm 0.205 in spacing



Features and Benefits

Save printing time with our large pre-printed cards offer with pre-printed numbers, letters or symbols.

Main Technical Data

Material	Flammability	Maximum printed digits		Dimensions	
		Horizontal	Vertical	mm	inches
Polyamide	V2			4.8 x 12	0.189 x 0.472

Ordering Details

Description	Number of markers per unit	Color	Type	Order Code	Pack ⁽ⁿ⁾ pieces	Weight (1 pce) g
0->9 (x10)	100	White	MC512PA	1SNK 140 091 R0000	1	10.00
1->10 (x10)	100	White	MC512PA	1SNK 140 011 R0000	1	10.00
11->20 (x10)	100	White	MC512PA	1SNK 140 021 R0000	1	10.00
21->30 (x10)	100	White	MC512PA	1SNK 140 031 R0000	1	10.00
31->40 (x10)	100	White	MC512PA	1SNK 140 041 R0000	1	10.00
41->50 (x10)	100	White	MC512PA	1SNK 140 051 R0000	1	10.00
51->60 (x10)	100	White	MC512PA	1SNK 140 061 R0000	1	10.00
61->70 (x10)	100	White	MC512PA	1SNK 140 071 R0000	1	10.00
71->80 (x10)	100	White	MC512PA	1SNK 140 081 R0000	1	10.00
81->90 (x10)	100	White	MC512PA	1SNK 140 083 R0000	1	10.00
91->100 (x10)	100	White	MC512PA	1SNK 140 101 R0000	1	10.00
101->110 (x10)	100	White	MC512PA	1SNK 140 111 R0000	1	10.00
111->120 (x10)	100	White	MC512PA	1SNK 140 121 R0000	1	10.00
121->130 (x10)	100	White	MC512PA	1SNK 140 131 R0000	1	10.00
131->140 (x10)	100	White	MC512PA	1SNK 140 141 R0000	1	10.00
141->150 (x10)	100	White	MC512PA	1SNK 140 151 R0000	1	10.00
151->160 (x10)	100	White	MC512PA	1SNK 140 161 R0000	1	10.00
161->170 (x10)	100	White	MC512PA	1SNK 140 171 R0000	1	10.00
171->180 (x10)	100	White	MC512PA	1SNK 140 181 R0000	1	10.00
181->190 (x10)	100	White	MC512PA	1SNK 140 191 R0000	1	10.00
191->200 (x10)	100	White	MC512PA	1SNK 140 201 R0000	1	10.00
1->100	100	White	MC512PA	1SNK 145 011 R0000	1	10.00
101->200	100	White	MC512PA	1SNK 145 021 R0000	1	10.00
201->300	100	White	MC512PA	1SNK 145 031 R0000	1	10.00
301->400	100	White	MC512PA	1SNK 145 041 R0000	1	10.00
401->500	100	White	MC512PA	1SNK 145 051 R0000	1	10.00
501->600	100	White	MC512PA	1SNK 145 061 R0000	1	10.00
601->700	100	White	MC512PA	1SNK 145 071 R0000	1	10.00
701->800	100	White	MC512PA	1SNK 145 081 R0000	1	10.00
801->900	100	White	MC512PA	1SNK 145 091 R0000	1	10.00
A (x100)	100	White	MC512PA	1SNK 146 011 R0000	1	10.00
B (x100)	100	White	MC512PA	1SNK 146 021 R0000	1	10.00
C (x100)	100	White	MC512PA	1SNK 146 031 R0000	1	10.00
D (x100)	100	White	MC512PA	1SNK 146 041 R0000	1	10.00
E (x100)	100	White	MC512PA	1SNK 146 051 R0000	1	10.00
F (x100)	100	White	MC512PA	1SNK 146 061 R0000	1	10.00
G (x100)	100	White	MC512PA	1SNK 146 071 R0000	1	10.00
H (x100)	100	White	MC512PA	1SNK 146 081 R0000	1	10.00
I (x100)	100	White	MC512PA	1SNK 146 091 R0000	1	10.00
J (x100)	100	White	MC512PA	1SNK 146 101 R0000	1	10.00
K (x100)	100	White	MC512PA	1SNK 146 111 R0000	1	10.00
L (x100)	100	White	MC512PA	1SNK 146 121 R0000	1	10.00
M (x100)	100	White	MC512PA	1SNK 146 131 R0000	1	10.00
N (x100)	100	White	MC512PA	1SNK 146 141 R0000	1	10.00
O (x100)	100	White	MC512PA	1SNK 146 151 R0000	1	10.00
P (x100)	100	White	MC512PA	1SNK 146 161 R0000	1	10.00
Q (x100)	100	White	MC512PA	1SNK 146 171 R0000	1	10.00
R (x100)	100	White	MC512PA	1SNK 146 181 R0000	1	10.00
S (x100)	100	White	MC512PA	1SNK 146 191 R0000	1	10.00
T (x100)	100	White	MC512PA	1SNK 146 201 R0000	1	10.00
U (x100)	100	White	MC512PA	1SNK 146 211 R0000	1	10.00
V (x100)	100	White	MC512PA	1SNK 146 221 R0000	1	10.00
W (x100)	100	White	MC512PA	1SNK 146 231 R0000	1	10.00

All the technical data for UL/CSA standard and dimensions in inches are in *italics*.

MC512PA Terminal Block Markers

Catalogue Page 1SNK 160 004 S0201

Pre-printed marker card for horizontal terminal block assembly



5.2 mm 0.205 in spacing



Ordering Details

Description	Number of markers per unit	Color	Type	Order Code	Pack ^(ing) pieces	Weight (1 pe)	g
X (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 146 241 R0000	1	10.00	
Y (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 146 251 R0000	1	10.00	
Z (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 146 261 R0000	1	10.00	
0 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 147 001 R0000	1	10.00	
1 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 147 011 R0000	1	10.00	
2 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 147 021 R0000	1	10.00	
3 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 147 031 R0000	1	10.00	
4 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 147 041 R0000	1	10.00	
5 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 147 051 R0000	1	10.00	
6 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 147 061 R0000	1	10.00	
7 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 147 071 R0000	1	10.00	
8 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 147 081 R0000	1	10.00	
9 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 147 091 R0000	1	10.00	
+ (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 001 R0000	1	10.00	
- (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 011 R0000	1	10.00	
~ (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 021 R0000	1	10.00	
= (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 031 R0000	1	10.00	
⊥ (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 041 R0000	1	10.00	
L1 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 051 R0000	1	10.00	
L2 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 061 R0000	1	10.00	
L3 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 071 R0000	1	10.00	
PE (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 091 R0000	1	10.00	
U1 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 101 R0000	1	10.00	
U2 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 111 R0000	1	10.00	
U3 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 121 R0000	1	10.00	
V1 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 131 R0000	1	10.00	
V2 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 141 R0000	1	10.00	
V3 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 151 R0000	1	10.00	
W1 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 161 R0000	1	10.00	
W2 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 171 R0000	1	10.00	
W3 (x100)	100	White <input type="checkbox"/>	MC512PA	1SNK 148 181 R0000	1	10.00	
L1-L2-L3-N-PE (x20)	100	White <input type="checkbox"/>	MC512PA	1SNK 149 001 R0000	1	10.00	
U1-U2-U3-V1-V2-V3-W1-W2-W3 (x10) + U1 (x10)	100	White <input type="checkbox"/>	MC512PA	1SNK 149 011 R0000	1	10.00	

All the technical data for UL/CSA standard and dimensions in inches are in *italics*.