

Impact Wrench LXT®

DTW1001

18V • 3/4" • 1 050 Nm • 0 – 1 800 min⁻¹

High torque, brushless impact wrench with two power settings for heavy-duty work

A powerful, brushless 3/4" drive impact wrench with a fastening torque of up to 1 050 Nm. Three different power settings. Equipped with an LED light for added lighting, this tool is ideal for applications that require high fastening torque.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Max Fastening Torque Impact Drill	300 / 600 / 1250 Nm
No load speed	0 - 900 / 1000 / 1800 min ⁻¹
Impacts per Minute (IPM)	0 - 1800 / 2000 / 2200 min ⁻¹
Drive Square	3/4 "
Tightening Capacity Standard Bolt	M12 - M30
Sound Power Level (L _{WA})	109 dB(A)
Sound Pressure Level (L _{pA})	101 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	3,4 - 3,7 kg
Product Dimensions (L x W x H):	229 x 91 x 289 mm
Brushless Motor	✓

User benefits

- Brushless maintenance-free and long-life motor
- LED light illuminates the work site
- Wide hanging hook, e.g. for scaffolding
- Battery protection system automatically shuts off power when the battery level is low
- Electronic 3 stage impact power selection
- Electric brake for maximum productivity and increased operator safety

Link to product - www.makitauk.com



Related products

■ Optional AC

191G67-2
Extension handle



450128-8
Battery cover, LXT®, 14,4 – 18V



821551-8
Makpac case (3)



837645-9
MakPac (3) Inlay



■ Other

User manual

Parts drawing