

## MNX ABS 150/50 LG



Sample photo

**Order symbol:** ABS 150/50 LG  
**Product nbr:** 6082314  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074022905  
**El. number:**  
 Finland 3420545  
 Denmark 8212023233  
 Italy 7361075  
 Sweden 2535742

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		L	W	H	Rating:
mm:		180	130	50	<b>Electrical insulation:</b> Totally insulated <b>Halogen free (DIN/VDE 0472, Part 815):</b> Yes <b>Flammability Rating (UL 746 C 5):</b> UL 94 HB <b>Glow Wire Test (IEC 695-2-1) °C:</b> 650 <b>NEMA Class:</b> NEMA 1, 4, 4X, 6 <b>Ingress Protection (EN 60529):</b> IP 66/67 <b>Impact Resistance (EN 50102):</b> IK 07
inch:		7.1	5.1	2	
Materials:					
<b>Material:</b>		ABS			
<b>Gasket material:</b>		TPE			
<b>Base colour:</b>		RAL 7035			
<b>Cover colour:</b>		RAL 7035			
<b>Cover screws material:</b>		Polyamide			
<b>Cover screws colour:</b>		Grey			
Temperatures:					
<b>Short term:</b>		-40 ... 80 °C			
<b>Continuous:</b>		-40 ... 60 °C			
<b>Short term:</b>		-40 ... 175 °F			
<b>Continuous:</b>		-40 ... 140 °F			
Accessories:					
MIV 150		Mounting plate (Galvanized steel)			
MIN 10		DIN-15 Mounting rail			
MIN 15		DIN-15 Mounting rail			
MIV 10		DIN-35 Mounting rail			
MIV 15		DIN-35 Mounting rail			
FP A 150/180		Front plate (Aluminium)			
HFP 180		Front plate hinge series (2 pcs)			
FP 22046		Wall fastening lug (4 pcs)			

**Certificates:**  
 Fimko  
 Europe EN 50298: 1998  
 Gost R

