



Part Number : [1301460149](#)

Product Description : Watertite Extyreme
Receptacle with Single Flip Coverplate with Locking
Blade, 2 Pole/3 Wire, NEMA L5-15, 125V

Series Number : 130146

Status : Active

Product Category : Wiring Devices

Engineering Number : 65W47



Documents & Resources

Drawings

[1301460149 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extyreme Receptacle with Single Flip Coverplate with Locking Blade, 2 Pole/3 Wire, NEMA L5-15, 125V
IP Rating	IP67
NEMA Configuration	NEMA L5-15
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871502

Agency

CSA	LR6837
UL	E68122

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Type	N/A
-----------	-----

Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Net Weight	387.821/g
Poles	2-pole/3-wire
Receptacle Type	Single