



MULTILINES LEVEL LASER 3X360° COMPACT XR 18V GREEN BEAM DCLE34031N-XJ

- Projection of 3 independent lines at 360°
- Green laser technology: up to 4 times more visible than red beams, even in a bright environment
- Pulsed diode compatible with DE0892G-XJ detector cell (not supplied)
- Ultra compact: compact design for working in small spaces
- Compatible with all DEWALT XR 18V series batteries, to use the same batteries as your DEWALT tools
- Memory: the laser keeps the last selected mode in memory and applies it at startup
- Magnetic base to attach the laser to any metal structure
- Wall stand with 1/4" and 5/8" thread for tripod adaptation and clamp location to fit all situations
- Compensator lock: protection of internal laser mechanism during transport



Type OF LINES	3x360° 1 horizontal line, 2 lvertical lines
Reach (with detection cell)	40m (100m)
Pulsed Mode	Yes, permanent
Accuracy	+/- 3mm up to 10m
Leveling range	± 4°
protection rating	IP54
tripod socket	1/4" & 5/8" (integrated in the support)
Supply	18V
Gencod	5035048749678

Equipment standard :
Livré sans batterie ni chargeur, cible, support mural,
coffret