

STANLEY

STANLEY Cubix™ 12m Cross Line Red Beam Laser

STHT77498-1



Features:

- 12m Working Range
- Accuracy of +/- 6mm @10m
- Projects 1 horizontal and 1 vertical line to create a cross line
- Can be flipped on its back for ceiling applications
- Self-levelling to +/-4°
- Rated to IP50 to protect against dust
- Pendulum lock for safe transportation
- 1/4" Thread allows the unit to be mounted to a tripod
- Suitable for internal use
- Runs on 2 x AA batteries (supplied)
- Includes QuickLink™ bracket system and soft pouch

Description:

The STANLEY Cubix™ Cross Line Red Beam Laser Level offers a 12m working range with an accuracy of +/- 6mm @10m. This red beam laser level projects 1 horizontal and 1 vertical line to create a cross line and can also be flipped on its back to make ceiling applications easy.

Specifications

Product Info	
SKU	STHT77498-1
Type	Cross Line
Beam Colour	Red
Line Accuracy	+/-6mm @10m
Line Range Visibility	12m
IP Rating	IP50
Warranty	1 Year
Batteries (Supplied)	2x AA Alkaline
Kit Contents	Stanley Bracket, Pouch