

## Datasheet

# RS Pro 3 Channel Digital DIN Rail Time Switch Measures Hours, 110 → 240 V ac

RS Stock No: **896-6882**



## Product Details

RS Pro time switch with 3 channel, supports 12/24 h display formats. This digital switch has a voltage rating of 110 to 240 V ac. This astro time switch is dynamic and has accurate control based on astronomical mathematics. The DIN rail switch features an easy manual override facility.

## Features and Benefits

- DIN rail mounting
- Backlit LCD display
- 12/24 hours display format
- Yearly programming with season mode, DST, offset, off hours enabled
- Latitude/longitude precise to the minute with time zone
- Sunrise/sunset or twilight rise/set trigger modes
- 1-phase
- High switching capacity



ENGLISH

### Specifications:

Units Measured	Hours
Battery Life	1000 h
Depth	67 mm
Height	90 mm
Number of Channels	3
Contact Configuration	2NO
Segment Length	1 min
Supply Voltage	110 to 240 V ac
Type	Digital
IP Rating	IP20, IP40
Number of Operating Modes	3