

HIGH SPEED DRILLING IN WOOD

EXPERT Self Cut Speed Spade Drill Bit

EXPERT

- ① Fast drilling is easier with Bosch Tip Technology
- ② Self-feeding thread for high-speed drilling with only a little pressure
- ③ Clever wave-shaped spade designed for fast chip removal



* vs. Bosch Spade Bit 2609255269



Video



BOSCH

EXPERT SELF CUT SPEED SPADE DRILL BIT



- Ideal for fast and rough drilling in all types of softwood, such as drilling through holes for cables, pipes, and other hardware installations. Easy to use in tight niches. Not suitable for hardwood
- Best for electricians and other installation workers: high speed and efficiency
- Up to 3x faster than Bosch 2609255269 Spade Bit
- 1/4" Impact rated Hex shank for use in impact driver and drill driver



PRODUCT PROPERTIES					ORDERING INFORMATION						
Diameter (D) mm	Working length mm	Total length mm	Shank diameter (d) mm	Shank diameter (d) Inch	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number		
Total length 152 mm											
6.00	100	152	6.35	1/4	PC1d	1	5	533 834	2 608 900 309		
Total length 400 mm											
6.00	350	406	6.35	1/4	PC1a	1	5	534 114	2 608 900 337		
Total length 152 mm											
8.00	100	152	6.35	1/4	PC1d	1	5	533 841	2 608 900 310		
Total length 400 mm											
8.00	350	406	6.35	1/4	PC1a	1	5	534 121	2 608 900 338		
Total length 152 mm											
10.00	100	152	6.35	1/4	PC1d	1	5	533 858	2 608 900 311		
Total length 400 mm											
10.00	350	406	6.35	1/4	PC1a	1	5	534 138	2 608 900 339		
Total length 152 mm											
12.00	100	152	6.35	1/4	PC1d	1	5	533 865	2 608 900 312		
Total length 400 mm											
12.00	350	406	6.35	1/4	PC1a	1	5	534 145	2 608 900 340		
Total length 152 mm											
13.00	100	152	6.35	1/4	PC1d	1	5	533 872	2 608 900 313		
Total length 400 mm											
13.00	350	406	6.35	1/4	PC1a	1	5	534 152	2 608 900 341		
Total length 152 mm											
14.00	100	152	6.35	1/4	PC1d	1	5	533 889	2 608 900 314		
Total length 400 mm											
14.00	350	406	6.35	1/4	PC1a	1	5	534 169	2 608 900 342		
Total length 152 mm											
16.00	100	152	6.35	1/4	PC1d	1	5	533 896	2 608 900 315		
Total length 400 mm											
16.00	350	406	6.35	1/4	PC1a	1	5	534 176	2 608 900 343		
Total length 152 mm											
17.00	100	152	6.35	1/4	PC1d	1	5	533 902	2 608 900 316		
Total length 400 mm											



BOSCH

EXPERT SELF CUT SPEED SPADE DRILL BIT

PRODUCT PROPERTIES					ORDERING INFORMATION				
Diameter (D) mm	Working length mm	Total length mm	Shank diameter (d) mm	Shank diameter (d) Inch	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number
17.00	350	406	6.35	1/4	PC1a	1	5	534 183	2 608 900 344
Total length 152 mm									
18.00	100	152	6.35	1/4	PC1d	1	5	533 919	2 608 900 317
Total length 400 mm									
18.00	350	406	6.35	1/4	PC1a	1	5	534 190	2 608 900 345
Total length 152 mm									
19.00	100	152	6.35	1/4	PC1d	1	5	533 926	2 608 900 318
Total length 400 mm									
19.00	350	406	6.35	1/4	PC1a	1	5	534 206	2 608 900 346
Total length 152 mm									
20.00	100	152	6.35	1/4	PC1d	1	5	533 933	2 608 900 319
Total length 400 mm									
20.00	350	406	6.35	1/4	PC1a	1	5	534 213	2 608 900 347
Total length 152 mm									
22.00	100	152	6.35	1/4	PC1d	1	5	533 940	2 608 900 320
Total length 400 mm									
22.00	350	406	6.35	1/4	PC1a	1	5	534 220	2 608 900 348
Total length 152 mm									
24.00	100	152	6.35	1/4	PC1d	1	5	533 957	2 608 900 321
Total length 400 mm									
24.00	350	406	6.35	1/4	PC1a	1	5	534 237	2 608 900 349
Total length 152 mm									
25.00	100	152	6.35	1/4	PC1d	1	5	533 964	2 608 900 322
Total length 400 mm									
25.00	350	406	6.35	1/4	PC1a	1	5	534 244	2 608 900 350
Total length 152 mm									
26.00	100	152	6.35	1/4	PC1d	1	5	533 971	2 608 900 323
Total length 400 mm									
26.00	350	406	6.35	1/4	PC1a	1	5	534 251	2 608 900 351
Total length 152 mm									
28.00	100	152	6.35	1/4	PC1d	1	5	533 988	2 608 900 324
Total length 400 mm									
28.00	350	406	6.35	1/4	PC1a	1	5	534 268	2 608 900 352
Total length 152 mm									
30.00	100	152	6.35	1/4	PC1d	1	5	533 995	2 608 900 325
Total length 400 mm									
30.00	350	406	6.35	1/4	PC1a	1	5	534 275	2 608 900 353
Total length 152 mm									
32.00	100	152	6.35	1/4	PC1d	1	5	534 008	2 608 900 326
Total length 400 mm									
32.00	350	406	6.35	1/4	PC1a	1	5	534 282	2 608 900 354
Total length 152 mm									
35.00	100	152	6.35	1/4	PC1d	1	5	534 015	2 608 900 327



BOSCH

EXPERT SELF CUT SPEED SPADE DRILL BIT

PRODUCT PROPERTIES					ORDERING INFORMATION					
Diameter (D) mm	Working length mm	Total length mm	Shank diameter (d) mm	Shank diameter (d) Inch	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number	
Total length 400 mm										
35.00	350	406	6.35	1/4	PC1a	1	5	534 299	2 608 900 355	
Total length 152 mm										
36.00	100	152	6.35	1/4	PC1d	1	5	534 022	2 608 900 328	
Total length 400 mm										
36.00	350	406	6.35	1/4	PC1a	1	5	534 305	2 608 900 356	
Total length 152 mm										
38.00	100	152	6.35	1/4	PC1d	1	5	534 039	2 608 900 329	
Total length 400 mm										
38.00	350	406	6.35	1/4	PC1a	1	5	534 312	2 608 900 357	
Total length 152 mm										
40.00	100	152	6.35	1/4	PC1d	1	5	534 046	2 608 900 330	
Total length 400 mm										
40.00	350	406	6.35	1/4	PC1a	1	5	534 329	2 608 900 358	



BOSCH