



Product data sheet

Power tools for trade & industry

Rotary Grinder

PRO GWG 12V-50 S



Compact, cordless, and powerful – The 12V grinder for numerous applications

The most important data

Battery voltage	12.0 V, 10.8 V
No-load speed	5,000 – 15,000 rpm
Weight excl. battery	0.53 kg

Order number 0 601 3A7 000

Technical data

Technical data

Battery voltage	12.0 V, 10.8 V
No-load speed	5,000 – 15,000 rpm
Packaging dimensions (width x length x height)	50 x 190 x 115 mm
Weight excl. battery	0.53 kg
Sanding pad diameter	50 mm



Product data sheet

Power tools for trade & industry

Advantages:

- Powerful, high-performance brushless motor and high torque enable high productivity
- Extremely lightweight and compact design with small grip size for fatigue-free working
- Variable-speed trigger switch and different speed modes enable perfect control for various tasks and optimal results



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/au/en/wac/>

