

Product information

ANGLE DRILL/DRIVER 10.8V



DA331DZ

Voltage	10.8 v
Max. in wood	12 mm
Battery Type	Lithium-ion
Charging Time	50 min
Vibration K factor	1.5 m/sec ²
Body only machine	1
Net weight	1.2 kg
Capacity	10 mm
Max cut in stainless steel	10 mm
No Load Speed	0-800 rpm
Vibration: Drilling into metal	2.5 m/sec ²



- Rubberized soft grip provides comfortable and sure grip.
- LED job light for improved work visibility.
- Easy-to-operate large paddle type switch with variable speed control.
- Keyless Chuck
- Electric brake

Details correct as of: 17-6-2014

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com