

Impact Wrench LXT®

DTW190

18V • M8 – M16 • 190 Nm • 0 – 2
300 min⁻¹

A handy wrench that is ideal for car wheel bolts

A compact and efficient impact wrench for M8 – M16 bolts. A small and light tool that is easy to use but offers a high fastening torque of up to 190 Nm. An ideal tool for changing car wheels. Additional lighting with a handy LED light.



LXT

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Max Fastening Torque Impact Drill	190 Nm
No load speed	0 - 2300 min ⁻¹
Impacts per Minute (IPM)	0 - 3000 min ⁻¹
Drive Square	1/2 "
Tightening Capacity Standard Bolt	M8 - M16
Tightening Capacity High Tensile Bolt	M8 - M12
Sound Power Level (L _{WA})	105 dB(A)
Sound Pressure Level (L _{pA})	97 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,4 - 1,8 kg
Product Dimensions (L x W x H):	176 x 79 x 237 mm
Nut-busting torque	320 Nm
Battery Chemistry (Ni-Cd / Ni-MH / Li-	Li-ion

User benefits

- The rubber coating on the handle ensures a firm working grip
- LED light illuminates the work site
- Battery protection system automatically shuts off power when the battery level is low
- Compact and lightweight for reduced operator fatigue
- Variable speed control by trigger for precise fastening in a wide variety of applications
- Electric brake for maximum productivity and increased operator safety

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing