



Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.5-1.5 mm <sup>2</sup>
Conductor cross section solid (solid, stranded)	0.5-2.5 mm <sup>2</sup>
Width	16 mm
Height	7 mm
Strip length	10 mm
MOQ	100 .
Unit	pcs
Nominal cross section	0.5-2.5 mm <sup>2</sup>
Length	16 mm
Nominal voltage	450 V

### **Approvals:**

Approved according to CE	Yes
Approved according to TUV	Yes
Approved according to UKCA	Ja

### **Compliance:**

Conflict Minerals	N/A, Contains no conflict minerals
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)

### **Other information:**

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Terminal Blocks
Search Description	SKV2025EJ1, ENR2025H, EFO2025H
Alternative SKU	PIC-30525
E-no	E1441351

### **Logistic information:**

Barcode	733117642077
Country of origin	CN
E-no	E1441351
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	100 .
Stock code	PIC-3 0525
Taric code	85369010
Unit	pcs

\*We reserve the right to make technical changes and disclaim any typographical errors.

---

**Nelco Contact AB** - Daléns Gata 7, 195 61 Arlandastad, Sweden - Tel. +46 (0)8 754 70 40 - [order@nelco.se](mailto:order@nelco.se) - [www.nelco.se](http://www.nelco.se)