

Item number: 56258

One Piece Shovel, D Grip, 1040 mm, Purple



Lightweight and durable shovel. Its one piece construction eliminates areas where bacteria can be harboured. Smooth surface makes it extremely easy to clean, ideal for use in food production areas for moving food ingredients or large quantities of food waste.

Technical data

EAN Number	5705020562587
DUN Number	15705020562584
Commodity Code	39241000
FDA compliant raw material (21)	Yes
Glass & Fork (EU 1935/2004), Declaration of Compliance, Regulation (EU) No 10/2011	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
Use of Phthalates & Bisphenol A	No
Material	Polypropylene
Shovel Blade Size, L x W	327 x 271 mm
Box Quantity	5 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	75 Pcs.
Colour	Purple
Height	120 mm
Length	1040 mm
Width	271 mm
Box Length	1190 mm
Box Height	365 mm
Box Width	265 mm
Gross Weight	1.455 kg.
Net Weight	1.26 kg
Country of origin	Denmark
Max cleaning temperature (Autoclave)	121 °Celsius
Max. cleaning temperature (Dishwasher)	93 °Celsius
Max. usage temperature (for food contact)	80 °Celsius
Max usage temperature (non food contact)	100 °Celsius
Min. usage temperature	-20 °Celsius
Max. drying temperature	120 °Celsius
Min. pH-value in usage concentration	2
Max. pH-value in Usage Concentration	10.5

New equipment should be cleaned, disinfected and sterilised, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.