



Specification
TEK100/TEK100YE/TEK101
Non-contact Voltage Indicator



Electrical

Voltage range: 100V to 600V AC rms (TEK100)
180V to 600V AC rms (TEK100YE & TEK101)
Frequency range: 45Hz to 1kHz
Voltage sensitivity: see table 1

Table 1. Typical Sensing Distances for Energised Cables at 50Hz

Cable Type	TEK100		TEK100YE & TEK101
	at 115V	at 230V	at 230V
Flat 1mm ² twin & earth	3mm	23mm	3 mm
Flat 2.5mm ² twin & earth	5mm	23mm	3 mm
Round 1.5mm ²	2mm	18mm	2 mm

Check out what else you can get from Martindale:

- 17th Edition Testers
- Accessories
- Calibration Equipment
- Continuity Testers
- Electricians' Kits
- Environmental Products
- Full Calibration & Repair Service
- Fuse Finders
- Digital Clamp Meters
- Digital Multimeters
- Labels
- Microwave Leakage Detectors
- Motor Maintenance Equipment
- Multifunction Testers
- Non-trip Loop Testers
- Pat Testers & Accessories
- Phase Rotation Testers
- Proving Units
- Socket Testers
- Thermometers & Probes
- Test Leads
- Voltage Indicators
- Specialist Metrohm Testers (4 & 5kV)
- Specialist Drummond Testers



Martindale Electric Company Limited
Metrohm House, Penfold Trading Estate, Imperial Way, Watford WD24 4YY, UK
Tel: +44 (0)1923 441717 Fax: +44 (0)1923 446900
E-mail: sales@martindale-electric.co.uk
Website: www.martindale-electric.co.uk



© 2014 Martindale Electric Company Ltd.
Registered in England No. 3387451. Rev 7 LIT100