



Product data sheet

Power tools for trade & industry

Impact Drill

PRO GSB 600



Upgraded 13 mm impact drill for even more power

The most important data

Rated input power	600 W
Drilling diameter in masonry	13 mm
Drilling diameter in wood	25 mm

Part Number 0 601 1A0 370

Technical data

Technical data

Rated input power	600 W
No-load speed, 1st gear	0 – 3,000 rpm
Power output	600 W
Weight	1.7 kg
Chuck capacity, min./max.	1.5 – 13 mm
Impact rate at no-load speed	0 – 48,000 bpm
Packaging dimensions (width x length x height)	255 x 287 x 71 mm

Drilling range

Drilling diameter in wood	25 mm
Drilling diameter in concrete	13 mm
Drilling diameter in steel	10 mm
Drilling diameter in masonry	13 mm

Noise/vibration information

Drilling in metal

Uncertainty K	1.5 m/s ²
---------------	----------------------

Impact drilling in concrete

Vibration emission value ah	25.3 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Better fixation thanks to additional ribs
- Longer usage ensured by improved carbon brush and high-quality design
- More efficiency with the robust and powerful upgraded 600 W motor



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

