

**Professionally approved products.**

## Spanner Set

# 5 Pc Metric Flexible Spanner Socket Set



[RS Stock No. 573-457](#)

### Material

Socket and handle: Chrome Vanadium steel (Cr-v #6140)

### Finish

Body of socket: Chrome plated

### Hardness

Heat treated to HRC- 42 ~ 48 degrees





## Professionally approved products.

### Contents

5 pc-Metric double ended flexible socket, chrome plated finished handle. Screw type flexible joint with ring (12 point socket) in Red colour pouch

### Size

8 mm x 9 mm (Overall length 200mm)

10 mm x 11 mm (Overall length 215 mm)

12 mm x 13 mm (Overall length 230 mm)

14 mm x 15 mm (Overall length 240 mm)

17 mm x 19 mm (Overall length 254 mm)

### Features

Specially designed to loosen and tighten nuts and bolts in confined spaces.

