



Housing units FLCTE35-XL (Series FLCTE)

two-bolt flanged housing units, cast iron, eccentric locking collar, P seals, without relubrication facility

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	35 mm
H	126 mm
U	42 mm
A ₁	22 mm
A ₂	12,4 mm
B ₁	39 mm
d _{3 max}	55 mm
J	100 mm
L	94 mm
N	11,5 mm
m	1,02 kg Mass

Cr	27500 N	Basic dynamic load rating, radial
C _{0r}	15300 N	Basic static load rating, radial
	LCTE07	Designation of housing
	RAE35-XL-NPP-B	Designation of bearing



