

A-10 ; 0...2.5 bar gauge; 0 ... 10 V, 3-wire @ 14...30 V DC

Pressure transmitter Model A-10

Item number: 12909913

Quantity: 1 pcs.

Order code: A-10-6-BG325-HD1Z-FC-AGZ-ZW W1011A10Z-SZ3S-ZZFWPA-3AZZZSAZZZA3Z

Overview: A-10 ; 0...2.5 bar gauge; 0 ... 10 V, 3-wire @ 14...30 V DC
Pressure transmitter Model A-10
Non-linearity: 0.5% BFSL
Process connection: G 1/4 A DIN EN ISO 1179-2; Sealing: NBR
Electrical connection: valve connector, size A
Pin assignment: U+=1, U-=2, S+=3
Permissible medium temperature: 0...+80 °C
Approvals: cULus
Type of packaging: folding box single
WIKA standard - specification according to data sheet PE 81.60

Details: Pressure transmitter Model A-10
for general applications
Specifications according to data sheet: PE 81.60
Wetted parts: 316L
Case: 316L
Non-linearity: 0.5% BFSL
Unit: bar
Pressure type: gauge
Measuring range: 0...2.5 bar gauge
Process connection: G 1/4 A DIN EN ISO 1179-2
Sealing: NBR
Permissible medium temperature: 0...+80 °C
Output signal: 0 ... 10 V, 3-wire
Power supply: 14...30 V DC
Electrical connection: valve connector, size A
Approvals: cULus
W1 (Wika standard)
Customer address: www.wika.com
Model name customer-specific: A-10
Pressure port: Standard
Type of packaging: folding box single
Sealing colour: WIKA standard (blue)
Test protocol: with test protocol
Main Language: English
Pin assignment: U+=1, U-=2, S+=3
Customer-specific: WIKA standard - specification according to data sheet
Model: A-10 2.0

Date: 23/01/2024



Operating Instructions: with printed OI
Additional Data: without